

ppe decontamination showers

A selection of Decontamination Showers used for the effective decontamination of Personal Protective Equipment.

ppe decontamination



DEC-V-5

Two stage Decontamination Shower with detergent application followed by wash down shower action. Incorporating a detergent inducing venturi feeding an overhead shower rose and hose brush, and 10 shower nozzle and hose brush, and 10 shower nozzles for the secondary wash down. Available with Stainless Steel pipework **DEC-V-5S.**

OPTIONAL FITTINGS:

- Drain Sump
- Flexible PVC strip screens fitted to entrance
- 38mm lay-flat delivery hose
- Galvanised painted panelling
- Stainless steel panelling
- Aluminium panelling



DEC-D-29

Basically similar to the Venturi Shower, but does not incorporate the venturi detergent inducer.

Available with Stainless Steel pipework **DEC-D-29S.**

OPTIONAL FITTINGS:

- Drain Sump
- Flexible PVC strip screens fitted to entrance
- 38mm lay-flat delivery hose
- Galvanised painted panelling
- Stainless steel panelling
- Aluminium panelling



DEC-V-1

Wall mounted Decontamination Shower with venturi detergent inducer. With tubulars manufactured from stainless steel milk tubing. For use in clean areas typically found in the pharmaceutical industry.

DEC-V-2

Wall mounted Decontamination Shower with venturi detergent inducer. With tubulars manufactured from stainless steel standard tubing.

DEC-V-3

Wall mounted Decontamination Shower with venturi detergent inducer. With tubulars manufactured from galvanised and painted carbon steel tubing.



When the location is of a temporary nature these units can be easily sited by Fork Lift Truck and connected to the water main by using 38mm lay-flat delivery hose.